

Wave Properties of light
06/11/08

Item	Manufacturer	Room	Cabinet	Qty.
Optical Rail	Spindler & Hoyer		In Rooms	1
Pin Carriers	Spindler & Hoyer	116	3	2
Laser on Rod	Homemade	112	7 "0"	1
Diffraction Scanner Apparatus	Homemade	112	12	1
ULI Cables*	Homemade	112	*	2
Metal (Yard) Ruler	C-Thru	116	3	1
Slits: Single, Double, and Multiple			In Rooms	1
Software: <i>Diffraction Scanner</i>			In Rooms	1
TV Diffraction		112	12	1/room

Notes: *ULI cables are hanging up on first row—DO NOT use cables with green band





